



Pass and Seymour
65W47 Turnlok Watertight Single Receptacle, Yellow
Part No. 65W47



Turnlok Watertight Single Receptacle, 15amp 125volt, NEMA Configuration L5-15, Impact resistant Valox lid, cover plate, and receptacle body withstand impacts, chemical, & corrosion.

Features & Benefits

Impact Resistant Valox lid, cover plate, and receptacle body withstand impacts, chemical & corrosion.

Stainless steel hinge spring and pin for corrosion resistance.

Spring loaded flip covers provide protection when device is not in use.

For Covering Patents, see www.legrand.us/patents.

Specifications

General Info

| | | | |
|-------------------|-----------------------|--------------|----------------|
| Color | Yellow | UPC Number | 785007033526 |
| Country Of Origin | United States | Product Line | Pass & Seymour |
| Standard | UL Listed, CSA Listed | | |

Listing Agencies / 3rd Party Agencies

| | |
|------------|-----|
| CSA Listed | Yes |
|------------|-----|

Technical Information

| | | | |
|-----------------|-------------|-----------|-------------------------|
| Number of Poles | Double Pole | Voltage | 124 V |
| Phase | Single | Wire Size | 18 AWG min - 12 AWG max |

Number of Wires

3

Environmental Conditions

Moisture Resistance NEMA 4, 4X, 12, 6, 6P/IP65, 66, 67 (Plug & Connector only)
Flammability UL94V0 (boxes & wiring device interiors)
Operating Temperature -40°C (without impact) to +60°C
continuous UV resistance All exposed materials are UV stabilized
