



Pass and Seymour
Turnlok® 65W49DPLX Watertight Single Receptacle, Yellow
Part No. 65W49DPLX



Turnlok Watertight Duplex Receptacle, 15amp 250volt, NEMA Configuration L6-15, Impact resistant Valox lid, cover plate, and receptacle body withstand impacts, chemical, and corrosion.

Features & Benefits

Impact Resistant Valox lid, cover plate, and receptacle body withstand impacts, chemical & corrosion.

Stainless steel hinge spring and pin for corrosion resistance.

Spring loaded flip covers provide protection when device is not in use.

For Covering Patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Yellow
UPC Number	785007032925	Country Of Origin	United States
Standard	UL Listed, CSA Listed		

Dimensions

Product Width US	1.85 in	Product Depth US	4.03 in
Product Height US	1.85 in		

Technical Information

Phase	Single	Number of Wires	3
Amperage	15 A	Number of Poles	Double Pole

Wire Size	18 - 12 AWG	Environmental Conditions	Moisture Resistance NEMA 4, 4X, 12, 6, 6P/IP65, 66, 67 (Plug & Connector only) Flammability UL94V0 (boxes & wiring device interiors) Operating Temperature -40°C (without impact) to +60°C continuous UV resistance All exposed material s are UV stabilized
-----------	-------------	--------------------------	---
