




Pass and Seymour
15A, 120V Trademaster® Single-Pole/Illuminated Toggle Switch, Ivory
Part No. 660ISLG



Trademaster® Single-Pole/Illuminated Toggle Switch

Features & Benefits

Quality Materials, durability, and time-tested design

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
Finish	Satin	UPC Number	785007663631
Country Of Origin	Mexico	Features	Extra Long Strap, Illuminated
Switch Type	Toggle	Number of Switches	1
Application Sector	Hospitality, Residential	Wall Plate Included	No
Standard	UL 20	Warranty Type	1-Year Limited Warranty
Type	Switch		

Dimensions

Product Width US	1.25 in	Product Depth US	1.09 in
Product Height US	4.195 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140597	cULus Listed	Yes
---------------------	--------	--------------	-----

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Load Rating	15 A @ 120 VAC	Connection Location	Side Only
-------------	----------------	---------------------	-----------

Terminal Accommodation	#14 AWG - #12 AWG	Number of Gangs	1
------------------------	-------------------	-----------------	---

Throw Type	Single Throw	Amperage	15 A
------------	--------------	----------	------

Number of Poles	Single Pole	Requires Neutral Wire	Yes
-----------------	-------------	-----------------------	-----

Indoor/Outdoor	Indoor	Mounting Type	Wall Box
----------------	--------	---------------	----------

Wire Connection Type	Push Wire	Voltage	120.0 V
----------------------	-----------	---------	---------

Load Type	CFL, Fluorescent, Halogen, Incandescent, LED, Universal, Xenon
-----------	---