



Pass and Seymour  
Trademaster® Grounding Toggle Switch  
Part No. 663WG

3-way Switch, Grounded, 15A, 120 volts



## Features & Benefits

Quality Materials, durability, and time-tested design

## Specifications

### General Info

Product Line	Pass & Seymour	Color	White
Finish	Satin	UPC Number	785007663105
Country Of Origin	China	Features	Extra Long Strap
Switch Type	Toggle	Number of Switches	1
Application Sector	Hospitality, Residential	Wall Plate Included	No
Standard	UL 498	Warranty Type	1-Year Limited Warranty
Type	Switch		

### Dimensions

Product Width US	1.25 in	Product Depth US	1.09 in
Product Height US	4.195 in		

## Listing Agencies / 3rd Party Agencies

CSA Listed	Yes
------------	-----

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Load Rating	15 A @ 120 VAC	Connection Location	Side Only
-------------	----------------	---------------------	-----------

Terminal Accommodation	#14 AWG - #12 AWG	Number of Gangs	1
------------------------	-------------------	-----------------	---

Throw Type	Single Throw	Amperage	15 A
------------	--------------	----------	------

Number of Poles	3-Way	Requires Neutral Wire	No
-----------------	-------	-----------------------	----

Indoor/Outdoor	Indoor	Mounting Type	Wall Box
----------------	--------	---------------	----------

Wire Connection Type	Push Wire	Voltage	120.0 V
----------------------	-----------	---------	---------

Load Type	CFL, Fluorescent, Halogen, Incandescent, LED, Universal, Xenon
-----------	---