



Pass and Seymour
Trademaster Grounding Toggle Switch, White, 100-Pack
Part No. 663WG100



Triple Pole Switch in white, with grounded terminals, is made with a thermoplastic toggle and frame. It has a smooth, quiet toggle action and is made with high-impact resistant construction. 15 amps, 120 volts. **Available in bulk packs of 90. Add 'U' to end of Catalog Number. Example: 663WGU

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	UPC Number	785007404456
Country Of Origin	China	Number of Switches	1
Application Sector	Residential	Standard	UL, CSA, FSUL
Type	Switch		

Dimensions

Product Width US	1.25 in	Product Height US	4.195 in
Product Length US	1.09 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Seismic Tested	No	Contact Rating	15 Amp, 120/125 VAC
Amperage	15 A	Number of Poles	3-Way
Wire Size	#14 - #10 AWG	Indoor/Outdoor	Indoor

Supply Voltage	120 V	Connection Type	Wired
Environmental Conditions	95% (relative humidity, non-condensing)		