



Pass and Seymour
Cover for 20A Turnlok® Watertight Receptacle
Part No. 6700



2.38\ diameter opening to accommodate a 20A Turnlok watertight receptacle.

Features & Benefits

Unbreakable glass-filled polycarbonate construction to withstand years of job site abuse and harsh environmental exposure.

Stainless steel mounting screws also resist corrosion.

Covers comply with 2005 NEC Section 406.8(A) and 406.8(B) (2).

Molded-in label area (2.8 sq. in.) for pre-printed or handwritten labels for identification of circuits, ratings and other application data.

WPG1 and WPG2 have lockable bullnose for OSHA locktag/tagout compliance.

Covers fit all competitive inlets and outlets.

Pre-attached gaskets for easy installation and tight seal to panel or weatherproof box -- with no misaligned or collapsed gaskets.

Tamper-proof hinge features permanent, locked-in pins for added security.

Specifications

General Info

Product Line	Pass & Seymour	Color	Yellow
Finish	Matte	UPC Number	785007040821
Country Of Origin	United States	Wall Plate Type	Custom
Application Sector	Commercial, Industrial	Warranty Type	1-Year Limited Warranty
Type	Wall Plate Accessories		

Dimensions

Product Width US	3.17 in	Product Depth US	2.62 in
------------------	---------	------------------	---------

Product Height US	4.92 in
-------------------	---------

Technical Information

Amperage	20 A	Indoor/Outdoor	Indoor
----------	------	----------------	--------

Mounting Type	Box Mounted
---------------	-------------
