



Single Pole, Double Switch, 20 amps, 120/277 volts, Ivory.



## Features & Benefits

Easily accessible break-off separate or common feed.

Long-life red neon lamp in pilot light rated 1/25 Watt, 125V.

Side wire #12 and #14 AWG.

Two devices fit into the space of one.

Grounding combination devices meet NEC Requirements. Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

Color	Ivory	UPC Number	785007670011
Country Of Origin	Mexico	Product Line	Pass & Seymour
Application Sector	Residential/Commercial	Type	Combination
Standard	UL20		

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes	cULus ListingNumber	140597
--------------	-----	---------------------	--------

### Technical Information

Number of Poles	Single Pole	Voltage	0.43321299639 V
-----------------	-------------	---------	-----------------

---

Actuator	Toggle	Contact Configuration	N-0
Connection	Side wire, non-grounding	Contact Rating	20 Amp, 120/277 VAC
Action	(2) SP	Environmental Conditions	Flammability: UL94 V2
Operating Cycles	30000		

---