



Features & Benefits

Easily accessible break-off separate or common feed.	Long-life red neon lamp in pilot light rated 1/25 Watt, 125V.
Side wire #12 and #14 AWG.	Two devices fit into the space of one.
Grounding combination devices meet NEC Requirements.	Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.

Specifications

General Info

Product Line	Pass & Seymour	Replaced by Part Number	671TRI
Color	Ivory	Country Of Origin	Mexico
Application Sector	Residential/Commercial	Standard	UL20, UL498
Type	Combination		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140597	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Contact Configuration	N-O	Operating Cycles	30000
Actuator	Toggle	Connection	Side wire
Contact Rating	120/125 VAC, 20 Amp	Amperage	20 A
Action	SP & Recptacle	Number of Poles	Single Pole
Voltage	120.0 V	Environmental Conditions	Flammability: UL94 V2