



Pass and Seymour
20A, 120/125V Combination Single-Pole Switch and Tamper-Resistant Single Receptacle, Brown
Part No. 671TR



Our standard Pass and Seymour combination switches allow you to add lights to any room in your home without having to add or replace wall boxes. This tamper-resistant version features a dual mechanical shutter system to help prevent the insertion of foreign objects, making it much safer and more convenient than plastic outlet caps. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

Features & Benefits

Easily accessible break-off separate or common feed.

Side wire #12 and #14 AWG.

Two devices fit into the space of one.

Grounding combination devices meet NEC Requirements.

Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Brown
Country Of Origin	Mexico	Application Sector	Residential/Commercial
Standard	UL20, UL498	Type	Combination

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140597	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Is Tamper-Resistant	Yes	Contact Configuration	N-0
Operating Cycles	30000	Actuator	Toggle
Connection	Side wire	Contact Rating	20 Amp, 120/125 VAC
Amperage	20 A	Action	SP & Recptacle

Number of Poles	Single Pole	Voltage	120.0 V
Environmental Conditions	Flammability: UL94 V2		