



## Legrand

20A, 120/125V Combination Single-Pole Switch & Tamper-Resistant Single Receptacle, Light Almond

Part No. 671TRLA



Our standard Pass & Seymour combination switches allow you to add lights to any room in your home without having to add or replace wall boxes. This tamper-resistant version features a dual mechanical shutter system to help prevent the insertion of foreign objects, making it much safer and more convenient than plastic outlet caps. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

### Features & Benefits

Easily accessible break-off separate or common feed.

Two devices fit into the space of one.

Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.

Side wire #12 and #14 AWG.

Grounding combination devices meet NEC Requirements.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

### Specifications

#### General Info

UPC Number 785007240740

Countries Of Origin Mexico

Product Line Pass & Seymour

Application Sector Residential/Commercial

Type Combination

Standard UL20, UL498

#### Listing Agencies / 3rd Party Agencies

cULus Listed Yes

cULus ListingNumber 140597

#### Technical Information

Number of Poles Single Pole

Voltage 120 V

Actuator Toggle

Contact Configuration N-0

---

<b>Connection</b>	Side wire
<b>Contact Rating</b>	20 Amp, 120/125 VAC
<b>Action</b>	SP & Receptacle
<b>Environmental Conditions</b>	Flammability: UL94 V2
<b>Operating Cycles</b>	30000

---