



Pass and Seymour  
**67W47 Turnlok Watertight Single Receptacle, Yellow**  
Part No. 67W47



Turnlok Watertight Single Receptacle, 20amp 125volt, NEMA Configuration L5-20, Impact resistant Valox lid, cover plate, and receptacle body withstand impacts, chemical, & corrosion.

## Features & Benefits

Impact Resistant Valox lid, cover plate, and receptacle body withstand impacts, chemical & corrosion.

Stainless steel hinge spring and pin for corrosion resistance.

Spring loaded flip covers provide protection when device is not in use.

For Covering Patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Yellow
UPC Number	785007033014	Country Of Origin	United States
Standard	UL Listed, CSA Listed		

### Listing Agencies / 3rd Party Agencies

CSA Listed	Yes
------------	-----

### Technical Information

Phase	Single	Number of Wires	3
Number of Poles	Double Pole	Wire Size	14 AWG min - 10 AWG max

---

Voltage

125 V

Environmental Conditions

Moisture Resistance NEMA 4, 4X, 12, 6, 6P/IP65, 66, 67 (Plug & Connector only)  
Flammability UL94V0 (boxes & wiring device interiors)  
Operating Temperature -40°C (without impact) to +60°C  
continuous UV resistance All exposed materials are UV stabilized

---