



Pass and Seymour
67W75 Turnlok Watertight Single Receptacle, Yellow
Part No. 67W75



Turnlok Watertight Single Receptacle, 30amp 3 250 volt, NEMA Configuration L15-20, Impact resistant Valox lid, cover plate, and receptacle body withstand impacts, chemical, & corrosion.

Features & Benefits

Impact Resistant Valox lid, cover plate, and receptacle body withstand impacts, chemical & corrosion.

Stainless steel hinge spring and pin for corrosion resistance.

Spring loaded flip covers provide protection when device is not in use.

For Covering Patents, see www.legrand.us/patents.

Specifications

General Info

Color	Yellow	UPC Number	785007033687
Country Of Origin	United States	Product Line	Pass & Seymour
Standard	UL Listed, CSA Listed		

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes
------------	-----

Technical Information

Number of Poles	3-Way	Voltage	250 V
Phase	Three	Wire Size	14 AWG min - 10 AWG max

Number of Wires

4

Environmental Conditions

Moisture Resistance NEMA 4,
4X, 12, 6, 6P/IP65, 66, 67 (Plug
& Connector only)
Flammability UL94V0 (boxes &
wiring device interiors)
Operating Temperature -40°C
(without impact) to +60°C
continuous UV resistance All
exposed material s are UV
stabilized
