



Pass and Seymour
Cover for 30A Turnlok® Watertight Receptacle
Part No. 6800



2.38\ diameter opening to accommodate a 30A Turnlok watertight receptacle.

Features & Benefits

Unbreakable glass-filled polycarbonate construction to withstand years of job site abuse and harsh environmental exposure.

Stainless steel mounting screws also resist corrosion.

Covers comply with 2005 NEC Section 406.8(A) and 406.8(B) [2].

Molded-in label area (2.8 sq. in.) for pre-printed or handwritten labels for identification of circuits, ratings and other application data.

WPG1 and WPG2 have lockable bullnose for OSHA locktag/tagout compliance.

Covers fit all competitive inlets and outlets.

Pre-attached gaskets for easy installation and tight seal to panel or weatherproof box -- with no misaligned or collapsed gaskets.

Tamper-proof hinge features permanent, locked-in pins for added security.

Specifications

General Info

Product Line	Pass & Seymour	Color	Yellow
Country Of Origin	United States		

Dimensions

Product Width US	3.17 in	Product Depth US	2.62 in
Product Height US	4.92 in		

Technical Information

Amperage

30 A
