



## Pass and Seymour

15A, 120/125V Decorator Combination Single-Pole Switch & Single Receptacle, White  
Part No. 681W



Our standard Pass & Seymour combination switches allow you to add lights to any room in your home without having to add or replace wall boxes.

### Features & Benefits

- Easily accessible break-off separate or common feed.
- Long-life red neon lamp in pilot light rated 1/25 Watt, 125V.
- Side wire #12 and #14 AWG.
- Two devices fit into the space of one.
- Grounding combination devices meet NEC Requirements.
- Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.

### Specifications

#### General Info

Color	White	UPC Number	785007006872
Country Of Origin	Mexico	Product Line	Pass & Seymour
Application Sector	Residential/Commercial	Type	Combination
Standard	UL20, UL498		

#### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes	cULus ListingNumber	140597
--------------	-----	---------------------	--------

#### Technical Information

Number of Poles	Single Pole	Voltage	120 V
Actuator	Toggle	Contact Configuration	N-0
Connection	Side wire	Contact Rating	15 Amp, 120/125 VAC
Action	SP & Recptacle	Environmental Conditions	Flammability: UL94 V2
Operating Cycles	30000		