



Single-Pole, Double Combination Switch, 15A, 120/277V, With Ground, Ivory.

## Features & Benefits

Easily accessible break-off separate or common feed.

Long-life red neon lamp in pilot light rated 1/25 Watt, 125V.

Side wire #12 and #14 AWG.

Two devices fit into the space of one.

Grounding combination devices meet NEC Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Ivory
Finish	Satin	UPC Number	785007690101
Country Of Origin	Mexico	Features	Combination
Switch Type	Toggle	Number of Switches	2
Application Sector	Hospitality, Residential	Wall Plate Included	No
Standard	UL 498	Warranty Type	1-Year Limited Warranty
Type	Combination, Switch, Tamper-Resistant		

## Dimensions

Product Width US	1.32 in	Product Depth US	0.94 in
Product Height US	4.06 in		
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	140597	cULus Listed	Yes
Technical Information			
Load Rating	15 A @ 120/277 VAC	Connection Location	Side Only
Terminal Accommodation	#14 AWG - #12 AWG	Number of Gangs	1
Throw Type	Single Throw	Amperage	15 A
Number of Poles	Single Pole	Requires Neutral Wire	Yes
Indoor/Outdoor	Indoor	Mounting Type	Wall Box
Wire Connection Type	Screw Terminals	Voltage	120 VAC, 277 VAC
Load Type	CFL, Fluorescent, Halogen, Incandescent, LED, Universal, Xenon		