




Pass and Seymour
15A 120V/125V Combination Single-Pole Toggle Switch and Single Receptacle, Brown
Part No. 691



Our standard Pass and Seymour combination switches allow you to add lights to any room in your home without having to add or replace wall boxes.

Features & Benefits

Easily accessible break-off separate or common feed.

Two devices fit into the space of one.

Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.

- One-piece heat-treated triple-wipe brass power contacts.
- Grounding combination devices meet NEC Requirements.

Specifications

General Info

Product Line	Pass & Seymour	Color	Brown
Finish	Matte	UPC Number	785007691009
Country Of Origin	Mexico	Number of Receptacles	1
Features	Combination	Number of Switches	1
Application Sector	Commercial, Residential	Standard	UL20, UL498
Type	Combination, Outlet, Switch		

Dimensions

Product Width US	1.32 in	Product Depth US	0.94 in
Product Height US	4.06 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140597	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Is Tamper-Resistant	No	Contact Configuration	N-O
---------------------	----	-----------------------	-----

Operating Cycles	30000	Connection	Side Wire
------------------	-------	------------	-----------

Contact Rating	15 Amp, 120/125 VAC	Amperage	15 A
----------------	---------------------	----------	------

Number of Poles	Single Pole	Wire Size	#14 - #10 AWG
-----------------	-------------	-----------	---------------

Is Weather Resistant	No	Indoor/Outdoor	Indoor
----------------------	----	----------------	--------

Mounting Type	Box	Supply Voltage	125 V
---------------	-----	----------------	-------

Voltage	120/125 V	Environmental Conditions	Flammability: UL94 V2
---------	-----------	--------------------------	-----------------------