



Pass and Seymour
15A 120V/125V Combination Single-Pole Toggle Switch and Single Receptacle, Light Almond
Part No. 691LA



Our standard Pass and Seymour combination switches allow you to add lights to any room in your home without having to add or replace wall boxes.

Features & Benefits

Easily accessible break-off separate or common feed.

Two devices fit into the space of one.

Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.

One-piece heat-treated triple-wipe brass power contacts.

Grounding combination devices meet NEC Requirements.

Specifications

General Info

Product Line	Pass & Seymour	Color	Light Almond
Finish	Satin	UPC Number	785007691054
Country Of Origin	Mexico	Features	Combination
Switch Type	Toggle	Number of Switches	1
Application Sector	Hospitality, Residential	Wall Plate Included	No
Standard	UL20, UL498	Warranty Type	1-Year Limited Warranty
Type	Combination, Outlet, Switch		

Dimensions

Product Width US	1.32 in	Product Depth US	0.94 in
Product Height US	4.06 in		
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	140597	cULus Listed	Yes
Technical Information			
Load Rating	15 A @ 120/125 VAC	Seismic Tested	No
Contact Configuration	N-O	Operating Cycles	30000
Connection Location	Side Only	Terminal Accommodation	#14 AWG - #12 AWG
Number of Gangs	1	Throw Type	Single Throw
Amperage	15 A	Number of Poles	Single Pole
Requires Neutral Wire	Yes	Indoor/Outdoor	Indoor
Mounting Type	Wall Box	Wire Connection Type	Screw Terminals
Voltage	120 VAC, 125 VAC	Load Type	CFL, Fluorescent, Halogen, Incandescent, LED, Universal, Xenon
Environmental Conditions	Flammability: UL94 V2		