



Legrand

15A, 120/125V Combination Single-Pole Switch & Single Receptacle, Light Almond

Part No. 691LA

Our standard Pass & Seymour combination switches allow you to add lights to any room in your home without having to add or replace wall boxes.



Features & Benefits

Easily accessible break-off separate or common feed.

Side wire #12 and #14 AWG.

Grounding combination devices meet NEC Requirements.

Long-life red neon lamp in pilot light rated 1/25 Watt, 125V.

Two devices fit into the space of one.

Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.

Specifications

General Info

UPC Number 785007691054

Countries Of Origin Mexico

Product Line Pass & Seymour

Application Sector Residential/Commercial

Type Combination

Standard UL20, UL498

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

cULus ListingNumber 140597

Technical Information

Number of Poles Single Pole

Voltage 120 V

Actuator Toggle

Contact Configuration N-0

Connection	Side wire
-------------------	-----------

Contact Rating	15 Amp, 120/125 VAC
-----------------------	---------------------

Action	SP & Receptacle
---------------	-----------------

Environmental Conditions	Flammability: UL94 V2
---------------------------------	-----------------------

Operating Cycles	30000
-------------------------	-------
