



Pass and Seymour
15A 120V/125V Combination Single-Pole Toggle Switch and Tamper-Resistant Single Receptacle, White
Part No. 691TRW



Our standard Pass and Seymour combination switches allow you to add lights to any room in your home without having to add or replace wall boxes. This tamper-resistant version features a dual mechanical shutter system to help prevent the insertion of foreign objects, making it much safer and more convenient than plastic outlet caps. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

Features & Benefits

Easily accessible break-off separate or common feed.	One-piece heat-treated triple-wipe brass power contacts.
Two devices fit into the space of one.	Grounding combination devices meet NEC Requirements.
Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.	For covering patents, see www.legrand.us/patents .

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Satin	UPC Number	785007240832
Country Of Origin	Mexico	Features	Combination
Switch Type	Toggle	Number of Switches	1
Application Sector	Hospitality, Residential	Wall Plate Included	No
Standard	UL20, UL498	Warranty Type	1-Year Limited Warranty
Type	Combination, Outlet, Switch, Tamper-Resistant		

Dimensions

Product Width US	1.32 in	Product Depth US	1.15 in
Product Height US	4.06 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140597	cULus Listed	Yes
Technical Information			
Load Rating	15 A @ 120/125 VAC	Contact Configuration	N-O
Operating Cycles	30000	Connection Location	Side Only
Terminal Accommodation	#14 AWG - #12 AWG	Number of Gangs	1
Throw Type	Single Throw	Amperage	15 A
Number of Poles	Single Pole	Requires Neutral Wire	Yes
Indoor/Outdoor	Indoor	Mounting Type	Wall Box
Wire Connection Type	Screw Terminals	Voltage	120 VAC, 125 VAC
Load Type	CFL, Fluorescent, Halogen, Incandescent, LED, Universal, Xenon		