



**Pass and Seymour**  
**15A, 120V/125V Combination Single-Pole Switch and Tamper-Resistant Single Receptacle, White**  
Part No. 691TRW



Our standard Pass & Seymour combination switches allow you to add lights to any room in your home without having to add or replace wall boxes. This tamper-resistant version features a dual mechanical shutter system to help prevent the insertion of foreign objects, making it much safer and more convenient than plastic outlet caps. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

## Features & Benefits

Easily accessible break-off separate or common feed.

Side wire #12 and #14 AWG.

Two devices fit into the space of one.

Grounding combination devices meet NEC Requirements.

Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	White
UPC Number	785007240832	Country Of Origin	Mexico
Application Sector	Residential/Commercial	Standard	UL20, UL498
Type	Combination		

### Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140597	cULus Listed	Yes
---------------------	--------	--------------	-----

### Technical Information

Contact Configuration	N-0	Operating Cycles	30000
Actuator	Toggle	Connection	Side wire
Contact Rating	15 Amp, 120/125 VAC	Action	SP & Recptacle

---

Number of Poles

Single Pole

Voltage

120 V

---

Environmental Conditions

Flammability: UL94 V2

---