



Double 3-way Combination Switch, 15A, 120/277V

Features & Benefits

Easily accessible break-off separate or common feed.

Long-life red neon lamp in pilot light rated 1/25 Watt, 125V.

Side wire #12 and #14 AWG.

Two devices fit into the space of one.

Grounding combination devices meet NEC Requirements. Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

| | | | |
|--------------------|------------------------|-------------------|--------|
| Product Line | Pass & Seymour | Color | White |
| UPC Number | 785007006155 | Country Of Origin | Mexico |
| Application Sector | Residential/Commercial | Standard | UL20 |
| Type | Combination | | |

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 140597 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

Technical Information

| | | | |
|-----------------------|-----|------------------|-------|
| Contact Configuration | N-0 | Operating Cycles | 30000 |
|-----------------------|-----|------------------|-------|

| | | | |
|----------------|---------------------|--------------------------|-----------------------|
| Actuator | Toggle | Connection | Side wire |
| Contact Rating | 15 Amp, 120/277 VAC | Amperage | 15 A |
| Action | (2) 3W | Number of Poles | 3-Way |
| Voltage | 0.433 V | Environmental Conditions | Flammability: UL94 V2 |
