

Single-Pole, 3-way Double Combination Switch, 15A 120/277V, Ivory.



Features & Benefits

Easily accessible break-off separate or common feed.

Side wire #12 and #14 AWG.

Two devices fit into the space of one.

Grounding combination devices meet NEC Requirements.

Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

| | | | |
|-------------------|----------------|--------------------|------------------------|
| Product Line | Pass & Seymour | Color | Ivory |
| Country Of Origin | Mexico | Application Sector | Residential/Commercial |
| Standard | UL20 | Type | Combination |

Dimensions

| | | | |
|-------------------|---------|------------------|---------|
| Product Width US | 1.32 in | Product Depth US | 0.94 in |
| Product Height US | 4.06 in | | |

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 140597 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

Technical Information

| | | | |
|--------------------------|-----------------------|------------------|-----------|
| Contact Configuration | N-0 | Operating Cycles | 30000 |
| Actuator | Toggle | Connection | Side wire |
| Contact Rating | 15 Amp, 120/277 VAC | Amperage | 15 A |
| Action | (1) SP & (1) 3W | Voltage | 0.433 V |
| Environmental Conditions | Flammability: UL94 V2 | | |