

Locking Plug Non-nema 2-Pole 3-Wire 20A 250V Gator Grip



Features & Benefits

- | | |
|---|--|
| Quick-thread assembly screws and cord-grip screws come backed-out, ready-to-wire. | Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity. |
| Raised ribs provide non-slip gripping profile for turning to lock and unlock. | Double dovetail design provides superior protection against cord pull-out forces. |
| Impact- and corrosion-resistant durable nylon 6 shell material. | Rounded back contour reduces snags and hang-ups on the job site. |
| Scallop shell design provides non-slip gripping surface for insertion and withdrawal. | Visible stamped NEMA configuration and device rating. |
| New-design external cord grips provide visible assurance of safe and proper cord retention. | Integral flexible rubber cord grommet conforms to and seals around SO cord to provide protection from oils, water, or chips entering wiring chamber. |

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
UPC Number	785007121032	Country Of Origin	United States
Application Sector	Industrial	Standard	UL Listed
Type	Plug Tail		

Dimensions

Product Width US	1.5 in	Product Length US	1.9 in
------------------	--------	-------------------	--------

Technical Information

Phase	Three	Number of Wires	3
Amperage	20 A	Number of Poles	Double Pole