



Pass and Seymour  
Turnlok® Industrial Spec Grade 20A Non-NEMA Flanged Inlet, Gray  
Part No. 7408SS

Flanged Outlet, Gray



### Features & Benefits

Interior components constructed of high-grade brass material for physical High-impact thermoplastic housing withstands and electrical integrity. on-the-job abuse.

Ratings and NEMA configurations are clearly visible on flange face, for fast I.D. while in use.

### Specifications

#### General Info

Product Line	Pass & Seymour	Country Of Origin	Mexico
Application Sector	Industrial	Standard	UL498

#### Dimensions

Product Width US	2.87 in	Product Depth US	1.65 in
Product Height US	2.87 in		

#### Technical Information

Phase	3	Number of Wires	4
Amperage	20 A	Number of Poles	4-Way
Wire Size	12 - 8 AWG	Voltage	125/250 V

---

Environmental Conditions	Consult the Factory
--------------------------	---------------------

---