



## Pass and Seymour Industrial Spec Grade Turnlok 20A Non-NEMA Connector, Yellow Part No. 7413G

Rely on Pass & Seymour Turnlok portable power solutions for all your demanding jobsite applications that require temporary power.



### Features & Benefits

Quick-thread assembly screws and cord-grip screws come backed-out, ready-to-wire.	Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity.
Raised ribs provide non-slip gripping profile for turning to lock and unlock.	Double dovetail design provides superior protection against cord pull-out forces.
Impact- and corrosion-resistant durable nylon 6 shell material.	Rounded back contour reduces snags and hang-ups on the job site.
Scallop shell design provides non-slip gripping surface for insertion and withdrawal.	Visible stamped NEMA configuration and device rating.
New-design external cord grips provide visible assurance of safe and proper cord retention.	Integral flexible rubber cord grommet conforms to and seals around SO cord to provide protection from oils, water, or chips entering wiring chamber.

### Specifications

#### General Info

Color	Black	UPC Number	785007121063
Country Of Origin	Mexico	Product Line	Pass & Seymour
Application Sector	Industrial	Standard	UL Listed

#### Technical Information

Number of Poles	3-Way	Voltage	250 V
Phase	3	Number of Wires	4