

Receptacle Single 15A 125V Turnlok®



Features & Benefits

Interior components constructed of high-grade brass material for physical and electrical integrity. High-impact thermoplastic housing withstands on-the-job abuse.

Ratings and NEMA configurations are clearly visible on flange face, for fast I.D. while in use.

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
UPC Number	785007753509	Country Of Origin	United States
Number of Receptacles	1	Features	Brass Mounting Strap, Impact Resistant
Outlet Type	Locking	Application Sector	Commercial
Wall Plate Included	No	Standard	UL 498
Warranty Type	1-Year Limited Warranty		

Dimensions

Product Width US	1.562 in	Product Depth US	0.922 in
Product Height US	1.75 in		

Technical Information

Connection Location	Back and Side	Number of Wires	2
Amperage	15 A	Number of Poles	Double Pole
Wire Size	14 - 10 AWG	Indoor/Outdoor	Indoor
NEMA Configuration Code	L1-15R	Wire Connection Type	Screw Terminals
Voltage	125.0 V		
