

Receptacle Duplex 15A 125V 10A 250V Turnlok®



Features & Benefits

Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.

One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.

Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.

Accepts #14 - #10 AWG.

Face color coding by voltage facilitates locating and mating of proper devices.

Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.

Side and external screw-pressure-plate back wire capability.

Specifications

General Info

Product Line	Pass & Seymour	Color	Brown
UPC Number	785007758009	Country Of Origin	Mexico
Number of Receptacles	2	Features	Brass Mounting Strap, Impact Resistant
Application Sector	Industrial	Wall Plate Included	No
Standard	Non-NEMA	Warranty Type	1-Year Limited Warranty

Dimensions

Product Width US	1.437 in	Product Depth US	0.97 in
Product Length US	2.3 in		

Technical Information

Connection Location	Back and Side	Number of Wires	3
Amperage	15 A	Wire Size	#14 - #10 AWG
Indoor/Outdoor	Indoor	Wire Connection Type	Screw Terminals
Voltage	125/250 V	Environmental Conditions	Consult the Factory
