



Wiremold
CabinetMate Plug-In Outlet Center Unit / 120V/20A/77 long/12 O/L /15' cord
Part No. 7712ULBD20R



Twelve 20A outlets with t-slots, 15' (4.6m) cord. Length 77" (2m). Receptacle center-to-center 6" (152mm). 20 Amp unit with a 20A resettable circuit breaker.

Features & Benefits

Twelve 20A outlets with t-slots, 15' (4.6m) cord. Length 77" (2m). Receptacle center-to-center 6" (152mm). 20 Amp unit with a 20A resettable circuit breaker.

Specifications

General Info

Product Line	Wiremold	UPC Number	786776052602
Country Of Origin	Mexico	Receptacle Type	Simplex
Number of Receptacles	12	Application Sector	Commercial
Standard	cULus Recognized: File E66421 Guide XBYS XUHT VZCA	Type	PIOC

Dimensions

Product Width US	1.5 in	Product Length US	77.0 in
------------------	--------	-------------------	---------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E66421	cULus Listed	Yes
---------------------	--------	--------------	-----

Buy American Act Compliance

NAFTA	Yes
-------	-----

Additional Information

RoHS Conformant Yes

Technical Information

Phase Single Frequency Rating 60 Hz

Amperage 20 A Enclosure Type Aluminum

Mounting Type Spring Clip Voltage 125.0 V

Environmental Conditions Dry interior locations
