

Direct mount shallow box with rotating dual support. 24-Pack.



Features & Benefits

Direct mount to joist.

Peel-off tape for "hands-free" installation.

Ground screw pre-installed.

Boxes include top knockouts.

5/8" depth.

UL listed for fan and fixture support.

Broadest line available, from shallow to deep boxes.

Supplied with hardware.

8 cubic inch volume.

Rated up to 70 pounds for fans, 150 pounds for fixture at 16" span.

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
Country Of Origin	China	Features	Fan Rated, Fixture Rated, Shallow
Application Sector	Commercial, Residential	Warranty Type	1-Year Limited Warranty
Type	Ceiling Box		

Dimensions

Product Width US	4.0 in	Product Depth US	0.625 in
------------------	--------	------------------	----------

Technical Information

Number of Gangs	1	Indoor/Outdoor	Indoor
Cable Entry	Back	Box Shape	Round

Mounting Type	Stud Mount
---------------	------------
