



# Pass and Seymour

## Double Pole, Single Phase AC Manual Controller

Part No. 7802MD

Double pole, Single Phase AC Manual Motor Controller 30 amp, 600 watts., Suitable as Motor Disconnect - 10KA @ 600VAC, 30A max Class J fuse.



### Features & Benefits

- High Horsepower rating of 20HP
- Constructed of glass-reinforced thermoplastic
- Heavy-duty zinc-plated steel strap, two brass rivets secure strap to housing
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).
- Gull-wing shaped brass terminal pressure clamps
- UL508 and cULus Listing of individual device and assembled device within enclosure
- External screw-pressure-plate back and side wire terminal screws unstaked for use with ring terminals
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

### Specifications

#### General Info

UPC Number	785007267655	Country Of Origin	Mexico
Product Line	Pass & Seymour	Standard	CSA Listed, UL Listed

#### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

#### Technical Information

Voltage	600 V	Actuator	Toggle
Connection	Side & Back Wired	Environmental Conditions	UL94 V2
Operating Cycles	50000		