



NEMA 1 Nylon Enclosure with 1/2inch and 3/4inch Knockouts

Features & Benefits

High horsepower rating of 20HP. Compact design. Gull-wing shaped brass terminal pressure clamps. Constructed of glass-reinforced thermoplastic. Two-point contact arms. One-piece contact carrier.

External screw-pressure-plate back and side wire terminal screws unstaked for use with ring terminals. Oversized silver alloy contacts.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

UL508 and cULus Listing of individual device and assembled device within enclosure. Heavy-duty zinc-plated steel strap. Two brass rivets secure strap to housing.

2-3/4 inch hubs (7812-EX and 7813-EX). 2-1/2 inch knockouts on back and 2-1/2 inch -3/4 inch knockouts on top and bottom (7812-P, 7813-P, 7806-P). 2-1/2 inch knockouts on bottom and back (7832 and 7833).

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
Finish	Matte	UPC Number	785007780659
Country Of Origin	Mexico	Standard	UL Listed
Type	Manual Controller		

Dimensions

Product Width US	2.825 in	Product Height US	3.91 in
------------------	----------	-------------------	---------

Technical Information

Connection	Side & Back Wired	Amperage	30 A
Wire Size	#14 - #10 AWG	Wattage	1 W
Voltage	600.0 V		
