



Pass and Seymour
Manual Controller
Part No. 7813EX



Triple-Pole, Three Phase Switch (7803) in a NEMA 7 and 9 Enclosure for Hazardous Locations. Class I - Groups C, D Class II - Groups E, F, G. 30A, 600Vs. Slotted opening on enclosures allows for lock-out, tag-out functionality.

Features & Benefits

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

Specifications

General Info

| | | | |
|--------------------|------------------------|---------------------|-------------------------|
| Product Line | Pass & Seymour | Color | Gray |
| Finish | Matte | UPC Number | 785007781342 |
| Country Of Origin | United States | Features | Enclosed |
| Switch Type | Toggle | Number of Switches | 1 |
| Application Sector | Commercial, Industrial | Wall Plate Included | No |
| Standard | UL Listed | Warranty Type | 1-Year Limited Warranty |
| Type | Manual Controller | | |

Dimensions

| | | | |
|-------------------|----------|------------------|---------|
| Product Width US | 3.375 in | Product Depth US | 4.25 in |
| Product Height US | 5.875 in | | |

Listing Agencies / 3rd Party Agencies

| | | | |
|------------|-----|-----------------|-------|
| CSA Listed | Yes | CSA File Number | 17949 |
|------------|-----|-----------------|-------|

Technical Information

| | | | |
|-------------|----------------|---------------------|---------------|
| Load Rating | 30 A @ 600 VAC | Connection Location | Back and Side |
|-------------|----------------|---------------------|---------------|

| | | | |
|------------------------|-------------------|-----------------|---|
| Terminal Accommodation | #14 AWG - #10 AWG | Number of Gangs | 1 |
|------------------------|-------------------|-----------------|---|

| | | | |
|------------|--------------|----------|------|
| Throw Type | Triple Throw | Amperage | 30 A |
|------------|--------------|----------|------|

| | | | |
|-----------------|-------|-----------------------|-----|
| Number of Poles | 3-Way | Requires Neutral Wire | Yes |
|-----------------|-------|-----------------------|-----|

| | | | |
|----------------|------|---------------|---------|
| Indoor/Outdoor | Both | Mounting Type | On-Wall |
|----------------|------|---------------|---------|

| | | | |
|----------------------|-----------------|---------|---------|
| Wire Connection Type | Screw Terminals | Voltage | 600.0 V |
|----------------------|-----------------|---------|---------|

| | |
|-----------|---|
| Load Type | CFL, Fluorescent, Halogen, Incandescent, LED, Universal, Xenon |
|-----------|---|