



## Pass and Seymour Three Pole Three Phase AC Manual Motor Controller Part No. 7813PMD



AC Manual Motor Controller, suitable as Motor Disconnect - 10KA @ 600VAC, 30A max. Class J Fuse.

### Features & Benefits

High Horsepower rating of 20HP	Gull-wing shaped brass terminal pressure clamps
Constructed of glass-reinforced thermoplastic	UL508 and cULus Listing of individual device and assembled device within enclosure
Heavy-duty zinc-plated steel strap, two brass rivets secure strap to housing	External screw-pressure-plate back and side wire terminal screws unstaked for use with ring terminals
For covering patents, see <a href="http://www.legrand.us/patents">www.legrand.us/patents</a> .	For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, <a href="#">click here</a> .

### Specifications

#### General Info

Color	Black	UPC Number	785007267693
Country Of Origin	Mexico	Product Line	Pass & Seymour
Standard	CSA Listed, UL Listed		

#### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

#### Technical Information

Voltage	600 V	Actuator	Toggle
Connection	Side & Back Wired	Enclosure Type	NEMA 1
Environmental Conditions	UL94 V2	Operating Cycles	50000