



Pass and Seymour
Manual Controllers
Part No. 7830



Nema 3R Enclosure Aluminum

Features & Benefits

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here.

Specifications

General Info

Product Line	Pass & Seymour	Color	Aluminum
Finish	Matte	UPC Number	785007078305
Country Of Origin	United States	Features	Enclosed
Switch Type	Toggle	Number of Switches	1
Application Sector	Commercial, Industrial	Wall Plate Included	No
Warranty Type	1-Year Limited Warranty	Type	Manual Controller

Listing Agencies / 3rd Party Agencies

cUL ListingNumber	31169	cUL Listed	Yes
-------------------	-------	------------	-----

Technical Information

Load Rating	30 A @ 600 VAC	Connection Location	Back and Side
-------------	----------------	---------------------	---------------

Terminal Accommodation	#14 AWG - #10 AWG	Number of Gangs	1
Throw Type	Triple Throw	Amperage	30 A
Number of Poles	3-Way	Requires Neutral Wire	Yes
Indoor/Outdoor	Both	Mounting Type	On-Wall
Wire Connection Type	Screw Terminals	Voltage	600.0 V
Load Type	CFL, Fluorescent, Halogen, Incandescent, LED, Universal, Xenon		