



Pass and Seymour
Manual Controller
Part No. 7833MD



Three pole, Three Phase AC Manual Motor Controller 30 amp, 600 watts., Suitable as Motor Disconnect - 10KA @ 600VAC, 30A max Class J fuse.

Features & Benefits

- High Horsepower rating of 20HP
- Constructed of glass-reinforced thermoplastic
- Heavy-duty zinc-plated steel strap, two brass rivets secure strap to housing
- For covering patents, see www.legrand.us/patents.
- Gull-wing shaped brass terminal pressure clamps
- UL508 and cULus Listing of individual device and assembled device within enclosure
- External screw-pressure-plate back and side wire terminal screws unstaked for use with ring terminals
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Specifications

General Info

Color	Aluminum	UPC Number	785007267709
Country Of Origin	Mexico	Product Line	Pass & Seymour
Standard	CSA Listed, UL Listed		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Voltage	600 V	Actuator	Toggle
Connection	Side & Back Wired	Enclosure Type	NEMA 3R
Environmental Conditions	UL94 V2	Operating Cycles	50000