



Pass and Seymour  
Manual Controller  
Part No. 7842MD



Double-Pole, Single Phase Switch (7842), 40 Amps, 600Vs

## Features & Benefits

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Black
Country Of Origin	Mexico	Standard	CSA Listed, UL Listed

### Dimensions

Product Width US	1.825 in	Product Depth US	1.753 in
Product Height US	3.67 in		

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

### Technical Information

Operating Cycles	50000	Actuator	Toggle
Connection	Side & Back Wired	Amperage	40 A
Voltage	600.0 V	Environmental Conditions	UL94 V2