



Pass and Seymour
Manual Controller
Part No. 7843MD



Triple-Pole, Three Phase Switch (7843), Canada Only Motor Disconnect. 40 amps, 600Vs.

Features & Benefits

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
Country Of Origin	Mexico	Standard	CSA Listed, UL Listed

Dimensions

Product Width US	1.825 in	Product Depth US	1.753 in
Product Height US	3.67 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Operating Cycles	50000	Actuator	Toggle
Connection	Side & Back Wired	Amperage	40 A
Voltage	600.0 V	Environmental Conditions	UL94 V2