



Pass and Seymour  
Manual Controllers  
Part No. 7863

Manual Control Switch 3pole 60amp 600volt



### Features & Benefits

High horsepower rating, up to 3HP for heavy-duty applications. Compact design provides ease of installation. Box lug terminals. Single piece moveable and stationary contact arms with oversized silver cadmium buttons provides excellent continuity and long life. Made in USA. Wire pockets and thick wall arc barriers. Cold-rolled steel NEMA 3R enclosure with polyester urethane finish conforms to OSHA lockout requirements. Type 3R enclosure has 2-1/2 inch, 3/4 inch, and 1 inch concentric knockouts on bottom. Accepts #4 AWG. cULus listed.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here.

### Specifications

#### General Info

|              |                |                   |              |
|--------------|----------------|-------------------|--------------|
| UPC Number   | 785007078633   | Country Of Origin | France       |
| Product Line | Pass & Seymour | Standard          | cULus Listed |

#### Listing Agencies / 3rd Party Agencies

|              |     |                     |        |
|--------------|-----|---------------------|--------|
| cULus Listed | Yes | cULus ListingNumber | 135325 |
|--------------|-----|---------------------|--------|

#### Technical Information

|         |     |         |       |
|---------|-----|---------|-------|
| Wattage | 3 W | Voltage | 600 V |
|---------|-----|---------|-------|