

Manual Control Switch 3-Pole 60A 600V



Features & Benefits

High horsepower rating, up to 3HP for heavy-duty applications. Compact design provides ease of installation. Single piece moveable and stationary contact arms with oversized silver cadmium buttons provides excellent continuity and long life.

Type 3R enclosure has 2-1/2 inch, 3/4 inch, and 1 inch concentric knockouts on bottom. Accepts #4 AWG. cULus listed.

Made in USA. Box lug terminals. Wire pockets and thick wall arc barriers. Cold-rolled steel NEMA 3R enclosure with polyester urethane finish conforms to OSHA lockout requirements.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007078633
Country Of Origin	France	Standard	cULus Listed
Type	Manual Controller		

Dimensions

Product Width US	1.74 in	Product Depth US	1.66 in
Product Height US	3.26 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	135325	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Amperage	60 A	Wire Size	#14 - #10 AWG
Voltage	600.0 V		
