



Pass and Seymour Manual Controllers Part No. 7863R



Manual Control Switch 3pole 60amp 600volt in NEMA 3R Enclosure. Slotted opening on enclosures allows for lock-out, tag-out functionality.

Features & Benefits

High horsepower rating, up to 3HP for heavy-duty applications. Compact design provides ease of installation. Box lug terminals. Single piece moveable and stationary contact arms with oversized silver cadmium buttons provides excellent continuity and long life. Made in USA. Wire pockets and thick wall arc barriers. Cold-rolled steel NEMA 3R enclosure with polyester urethane finish conforms to OSHA lockout requirements. Type 3R enclosure has 2-1/2 inch, 3/4 inch, and 1 inch concentric knockouts on bottom. Accepts #4 AWG. cULus listed.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here.

Specifications

General Info

Color	Gray	UPC Number	785007078640
Country Of Origin	United States	Product Line	Pass & Seymour
Standard	UL Listed		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes	cULus ListingNumber	31169
--------------	-----	---------------------	-------

Technical Information

Wattage	3 W	Voltage	600 V
---------	-----	---------	-------