



Heavy-Duty Hospital Grade Compact Design Duplex Receptacle Back and Side Wire 20A 125V



## Features & Benefits

|   |   |
|---|---|
| Impact-resistant nylon face.  | .032 inch thick, brass, triple-wipe power contacts for lasting retention.   |
| Easily accessible break-off line contact connecting tab for split circuit wiring.   | Corrosion-resistant, zinc-plated steel strap is locked in.  |
| Internal screw-pressure-plate back wire and side wire line terminals accept #14 : #10 AWG copper or copper-clad conductors. | High strength thermoplastic back body.  |
| Auto-ground clip assures positive ground.   | Compact design for easy installation.   |
| Tri-drive terminal and mounting screws.   | Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact |

## Specifications

### General Info

|                       |                         |                   |                    |
|-----------------------|-------------------------|-------------------|--------------------|
| Product Line          | Pass & Seymour          | Color             | Red                |
| Finish                | Matte                   | Country Of Origin | Mexico             |
| Number of Receptacles | 2                       | Outlet Type       | Commercial, Indoor |
| Application Sector    | Industrial              | Standard          | UL 498             |
| Warranty Type         | 1-Year Limited Warranty | Type              | Outlet             |

### Dimensions

---

|                  |          |                  |         |
|------------------|----------|------------------|---------|
| Product Width US | 1.322 in | Product Depth US | 0.78 in |
|------------------|----------|------------------|---------|

---

|                   |          |
|-------------------|----------|
| Product Height US | 3.281 in |
|-------------------|----------|

---

### Listing Agencies / 3rd Party Agencies

---

|                     |        |              |     |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 140596 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

---

### Technical Information

---

|          |      |                 |             |
|----------|------|-----------------|-------------|
| Amperage | 20 A | Number of Poles | Double Pole |
|----------|------|-----------------|-------------|

---

|           |       |                |        |
|-----------|-------|----------------|--------|
| Wire Size | 4 AWG | Indoor/Outdoor | Indoor |
|-----------|-------|----------------|--------|

---

|         |         |
|---------|---------|
| Voltage | 125.0 V |
|---------|---------|

---