



Pass and Seymour  
20A 125V Heavy Duty Hospital-Grade Compact Duplex Receptacle, Back and Side Wire, Red  
Part No. 8300HRED

Heavy-Duty Hospital Grade Compact Design Duplex Receptacle Back and Side Wire 20A 125V



## Features & Benefits

Impact-resistant nylon face.	.032 inch thick, brass, triple-wipe power contacts for lasting retention.
Easily accessible break-off line contact connecting tab for split circuit wiring.	Corrosion-resistant, zinc-plated steel strap is locked in.
Internal screw-pressure-plate back wire and side wire line terminals accept #14 : #10 AWG copper or copper-clad conductors.	High strength thermoplastic back body.
Auto-ground clip assures positive ground.	Compact design for easy installation.
Tri-drive terminal and mounting screws.	Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Red
Finish	Matte	UPC Number	785007830040
Country Of Origin	Mexico	Number of Receptacles	2
Application Sector	Commercial, Hospital Grade	Standard	UL 498, FEDSPEC
Warranty Type	1-Year Limited Warranty	Type	Outlet

### Dimensions

Product Width US	1.322 in	Product Depth US	0.78 in
------------------	----------	------------------	---------

Product Height US	3.281 in
-------------------	----------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Amperage	20 A	Number of Poles	Double Pole
Wire Size	4 AWG	Indoor/Outdoor	Indoor