



Wiremold
FLOOR BOX W/895TSP BRASS COVER
Part No. 862TSP

862 Series Residential Floor Boxes provide an excellent solution for the low density power or communication requirements in open space areas. Durable PVC construction and an innovative design allows the 862 Series Residential Floor Boxes to be installed in either wood or slab-on-grade concrete floors. 862 Series Floor Boxes are designed to work with a full range of forged, solid brass or brushed aluminum covers to accommodate a wide range of power and communication devices.

Features & Benefits

Includes 862 Series Floor Box, one 15A, 125V tamper-resistant brown duplex receptacle, and one 895TSP brass cover for tile. Cover provides two 1 1/2" [38mm] screw plug openings.

Specifications

General Info

| | | | |
|--------------------|---|----------------|--|
| Product Line | Wiremold | UPC Number | 786564032632 |
| Country Of Origin | Mexico | Cover Material | Brass |
| Application Sector | Commercial, Hospitality, Residential | Standard | cULus Listed Nonmetallic Outlet Boxes: File E110748 Guide QCMZ. Meets Article 314.27(C) of NEC. |
| Warranty Type | 1-Year from Installation or 2-Years from Day of Sale | Type | Floor Box |

Dimensions

| | | | |
|-------------------|---------|---------------|--------|
| Product Weight US | 2.04 lb | Knockout Size | 3/4 in |
|-------------------|---------|---------------|--------|

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------------|---------|--------------|-----|
| cULus ListingNumber | E110748 | cULus Listed | Yes |
|---------------------|---------|--------------|-----|

Trade Programs

| | |
|-------|-----|
| USMCA | Yes |
|-------|-----|

Additional Information

| | |
|----------------|-----|
| RoHS Compliant | Yes |
|----------------|-----|

Technical Information

| | | | |
|------------|----------------------|------------------|--------|
| Floor Type | Concrete, Tile, Wood | Service Capacity | Single |
|------------|----------------------|------------------|--------|

| | | | |
|--------------|--------|----------------------------|--------|
| Box Capacity | 1 Gang | Depth Behind Device Plates | 3.5 in |
|--------------|--------|----------------------------|--------|
