



The 880CS3-1 three gang Omnibox® Floor Box provides an excellent activation solution for applications where multiple services are required in open space areas. The 880CS3-1 floor box is offered in a stamped steel construction, designed to be installed in above grade concrete floor applications and to meet a wide range of market requirements. This floor box series has many applications, some of which are schools, financial institutions, and commercial office buildings.

Features & Benefits

TopGuard protection. All cover assemblies for the Omnibox Floor Box Series have TopGuard protection. An integral design which keeps out water, dirt, and debris from the power and communication compartments.

Watertight cast-iron construction. Meets requirements for on grade or below grade application Three-gang configurations, maximum flexibility. Can remove divider for greater capacity. Supports multiservice applications.

Flush activation assemblies for carpet and tile. Aesthetically pleasing assemblies are interchangeable for both cast-iron and stamped steel.

Fully adjustable box. Before and after concrete pour adjustability. Lower installed cost.

Boxes and covers have been listed by Underwriters Laboratories Inc. to their standard UL514A, 514C, 514D, and Canadian standard C22.2

Datacom connectivity options. Accepts industry standard and proprietary devices from a wide range of manufacturers to provide a seamless and aesthetically pleasing interface for voice, data, audio, and video applications at the point-of-use. A wide selection of data and bezel options available for use with Ortronics TracJack and Series II devices.

Specifications

General Info

| | | | |
|--------------------|--------------|---------------------|--|
| Product Line | Wiremold | Color | Silver |
| UPC Number | 786564515890 | Country Of Origin | China |
| Construction | Assembled | Number of Knockouts | 1 |
| Application Sector | Commercial | Standard | cULus Listed Metallic Outlet Boxes: File E2961 Guide QCIT. Meets Article 314.27(C) of NEC. |

| | |
|------|-----------|
| Type | Floor Box |
|------|-----------|

Dimensions

| | | | |
|------------------|---------|-------------------|---------|
| Product Width US | 5.38 in | Product Weight US | 13.4 lb |
|------------------|---------|-------------------|---------|

| | | | |
|-------------------|--------------|------------------|----------|
| Product Volume US | 265.31 cu in | Product Depth US | 14.63 in |
|-------------------|--------------|------------------|----------|

| | | | |
|-------------------|---------|----------------|-----------|
| Product Height US | 3.38 in | Cubic Capacity | 160 cu in |
|-------------------|---------|----------------|-----------|

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------------|-------|--------------|-----|
| cULus ListingNumber | E2961 | cULus Listed | Yes |
|---------------------|-------|--------------|-----|

Additional Information

| | | | |
|-----------------|-----|-------------------------------|-----|
| RoHS Conformant | Yes | Product Environmental Profile | Yes |
|-----------------|-----|-------------------------------|-----|

Technical Information

| | | | |
|-------------|--------------------|-------------------|---|
| Cable Entry | Conduit Threads in | Number of Outlets | 0 |
|-------------|--------------------|-------------------|---|
