



Pass and Seymour
Trademaster® 15A 125V Tamper-Resistant 8-Hole/Push Wire Duplex Receptacle, Brown
Part No. 880TR



Our Pass and Seymour TradeMaster receptacles combine a traditional look with reliable, time-tested operation for any residential application. This receptacle is also outfitted with our patented automatic shutter system to prevent young children from inserting common objects, such as hairpins or keys. The shutters release when a plug is inserted. Required by the National Electrical Code (NEC). For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

Features & Benefits

- Meets 2008 National Electrical Code Tamper-Resistant requirements. High-impact resistant thermoplastic construction.
- Extra-long strap.
- Long-term blade retention.
- Side-access push wire release.
- Traditional contoured face (3232 models).
- Quickloop wire looping aid.
- Extra-large circuit break-off tabs.
- Ultrasonic welding of face to back body.
- Self-grounding models provide automatic ground clip.

Specifications

General Info

Product Line	Pass & Seymour	Color	Brown
UPC Number	785007008388	Country Of Origin	Mexico
Number of Receptacles	2	Outlet Type	Tamper-Resistant
Application Sector	Commercial, Multi-Dwelling Unit, Residential	Wall Plate Included	No
Standard	UL498, CSA C22.2 No. 42	Warranty Type	1-Year Limited Warranty
Type	Outlet		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Additional Information

Product Environmental Profile Yes

Technical Information

Is Tamper-Resistant	Yes	Connection	Push wire
Number of Wires	3	Temperature Rating	-30° - 60° C
Amperage	15 A	Number of Poles	Double Pole
Wire Size	14 AWG	Indoor/Outdoor	Indoor
NEMA Configuration Code	5-15R	Wire Connection Type	Push Wire
Voltage	125.0 V	Environmental Conditions	Flammability: UL94 V2
