



Legrand

15A/125V TradeMaster Tamper-Resistant 8-Hole/Push Wire Receptacle, Brown
Part No. 880TR



Our Pass & Seymour TradeMaster receptacles combine a traditional look with reliable, time-tested operation for any residential application. This receptacle is also outfitted with our patented automatic shutter system to prevent young children from inserting common objects, such as hairpins or keys. The shutters release when a plug is inserted. Required by the National Electrical Code (NEC). For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

Features & Benefits

Meets 2008 National Electrical Code Tamper-Resistant requirements.	: Protects children: patented shutter system helps prevent improper insertion of foreign objects.
High-impact resistant thermoplastic construction.	Extra-long strap.
Quickloop wire looping aid.	Long-term blade retention.
: Longer tri-drive screws for easier 12 AWG looping.	Extra-large circuit break-off tabs.
Side-access push wire release.	Ultrasonic welding of face to back body.
Side wire accepts #12 : #14 AWG solid wire.	: Push wire accepts #14 AWG solid only.
Superior protection than traditional outlet caps or protection plates.	Low profile face.
Traditional contoured face (3232 models).	Self-grounding models provide automatic ground clip.

Specifications

General Info

Color	Brown
UPC Number	785007008388
Countries Of Origin	Mexico
Product Line	Pass & Seymour
Application Sector	Residential
Standard	UL498, CSA C22.2 No. 42

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Number of Poles Double Pole

Voltage 125 V

Connection Push wire

Temperature Rating Maximum continuous +60°C, minimum -30°C

Wire Size 14 AWG

Number of Wires 3

Environmental Conditions Flammability: UL94 V2
