



Pass and Seymour  
Trademaster® 15A 125V Tamper-Resistant 8-Hole/Push Wire Duplex Receptacle, White  
Part No. 880TRW



Our Pass and Seymour TradeMaster receptacles combine a traditional look with reliable, time-tested operation for any residential application. This receptacle is also outfitted with our patented automatic shutter system to prevent young children from inserting common objects, such as hairpins or keys. The shutters release when a plug is inserted. Required by the National Electrical Code (NEC). For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

## Features & Benefits

Meets 2008 National Electrical Code Tamper-Resistant requirements. High-impact resistant thermoplastic construction.

Extra-long strap.

Quickloop wire looping aid.

Long-term blade retention.

Extra-large circuit break-off tabs.

Side-access push wire release.

Ultrasonic welding of face to back body.

Traditional contoured face (3232 models).

Self-grounding models provide automatic ground clip.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	UPC Number	785007008371
Country Of Origin	Mexico	Number of Receptacles	2
Outlet Type	Tamper-Resistant	Application Sector	Commercial, Multi-Dwelling Unit, Residential
Wall Plate Included	No	Standard	UL498, CSA C22.2 No. 42
Warranty Type	1-Year Limited Warranty	Type	Outlet

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

---

Additional Information

---

Product Environmental Profile    Yes

---

Technical Information

---

Is Tamper-Resistant	Yes	Temperature Rating	-30° - 60° C
Amperage	15 A	Number of Poles	Double Pole
Wire Size	14 AWG	Indoor/Outdoor	Indoor
NEMA Configuration Code	5-15R	Wire Connection Type	Push Wire
Voltage	125.0 V		

---