



Pass and Seymour

Discontinued - Trademaster® 15A 125V Tamper-Resistant 8-Hole/Push Wire Duplex Receptacle, Without Ears, White

Part No. 880TRWMH



Our Pass & Seymour TradeMaster® receptacles combine a traditional look with reliable, time-tested operation for any residential application. This receptacle is also outfitted with our patented automatic shutter system to prevent young children from inserting common objects, such as hairpins or keys. The shutters release when a plug is inserted. Required by the National Electrical Code® (NEC®).

For detailed Tamper-Resistant receptacle information, visit our [Tamper-Resistant Receptacles page](#).

Features & Benefits

Meets 2008 National Electrical Code Tamper-Resistant requirements.

Extra-long strap.

Long-term blade retention.

Side-access push wire release.

Traditional contoured face (3232 models).

High-impact resistant thermoplastic construction.

Quickloop wire looping aid.

Extra-large circuit break-off tabs.

Ultrasonic welding of face to back body.

Self-grounding models provide automatic ground clip.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Country Of Origin	Mexico	Number of Receptacles	2
Outlet Type	Commercial, Indoor, Residential, Tamper-Resistant	Application Sector	Residential
Standard	UL498, CSA C22.2 No. 42	Type	Outlet

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Is Tamper-Resistant	Yes	Connection	Push wire
Number of Wires	3	Temperature Rating	-30° - 60° C
Amperage	15 A	Number of Poles	Double Pole
Wire Size	14 AWG	Indoor/Outdoor	Indoor

Voltage

125.0 V

Environmental Conditions

Flammability: UL94 V2
