




radiant Collection  
radiant® Tamper-Resistant Outlet, White  
Part No. 885TRW



Take a step up from the standard. This tamper-resistant duplex outlet installs easily for the basic power every home needs, while elevating your space with the sleek, clean lines of radiant® for a sophisticated look. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

## Features & Benefits

Replaces any standard outlet with ease, in as little as 10 minutes.

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

Features durable, high-impact resistant thermoplastic construction.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	Country Of Origin	China
Receptacle Type	5-15R	Number of Receptacles	2
Outlet Type	Indoor, Residential, Tamper-Resistant	Application Sector	Residential/Commercial
Standard	UL 498	Warranty Type	1-Year Limited Warranty
Type	Outlet		

## Dimensions

Product Width US	1.29 in	Product Depth US	1.0 in
Product Height US	4.2 in		
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	140596	cULus Listed	Yes
Additional Information			
Product Environmental Profile	Yes		
Technical Information			
Is Tamper-Resistant	Yes	Number of Gangs	1
Amperage	15 A	Number of Poles	Double Pole
Is Weather Resistant	No	Indoor/Outdoor	Indoor
NEMA Configuration Code	5-15R	Mounting Type	Box
Voltage	125.0 V	Environmental Conditions	95% (relative humidity, non-condensing)