

### Single-Pole Preset Wide Slide Dimmer 600W



## Features & Benefits

Maximum ratings are for continuous full load.

RFI suppression built in.

Preset ON/OFF switch automatically returns controlled lights to preset level without readjusting dimmer setting.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

Many 1000W models fit standard Decorator plates.

Full-On bypass.

600W maximum rated dimmers can be ganged without de-rating.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Ivory
UPC Number	785007906806	Country Of Origin	Mexico
Application Sector	Residential	Standard	RoHS, CSA Listed, UL Listed

### Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	48758
------------	-----	-----------------	-------

### Technical Information

Frequency Rating	120VAC 60Hz Hz	Connection	Screw Terminals
Number of Poles	Single Pole	Wattage	600 W

---

Voltage

120 V

Load

Incandescent

---

Environmental Conditions

Humidity: Less than 95% non  
condensing

---